



## Technical Specifications

The G5 GBM hand-held massager provides 15 to 55 CPS. It is ergonomically designed to reduce hand vibration. Use the G5 GBM massager for home use or light-duty clinic only.

G5 massage machines have been sold and used successfully for over 50 years. G5 massage machines are the only massagers with Directional Stroking<sup>®</sup>, not vibration.

The G5 GBM provides very deep penetrating massage. It is reliable, durable and quiet. Using the G5 GBM massage machine over a hot pack or cold pack seems to drive in the heat or cold. It can be equally-effective when used over towelings or clothing, and won't tangle in hair.

Accessories include: 1- four-ball applicator (AP216); 1-Two-Ball Applicator (AP223); 1- pointed-tip applicator (AP227); 1 large 5" diameter firm rubber applicator (AP229); 1- curved sponge applicator (AP230); 25-medium disposable applicator covers (AP235D) and; 25-large disposable



|                       |                            |
|-----------------------|----------------------------|
| Motor -               | 1/40 horsepower            |
| Output Speed -        | 15 to 55 cycles per second |
| Power Source -        | 90 - 240 VAC 50/60 H       |
| Speed Control -       | Solid State Electronic     |
| Leakage Current -     | under 75 $\mu$ A           |
| Unit Length -         | 10-inches                  |
| Unit Weight -         | 3 Lbs. 10 oz.              |
| Applicator Packages - | PRO-PORT-PKG (60002)       |
| Shipping Weight -     | 10 lbs.                    |